

PHONE PLUGS & JACKS

Note: Unless otherwise specified, plug and jack exposed metal parts are normally bright nickel plated, Soldering tabs and lugs are usually tinned brass for best solder joints; except in case where gold or silver is used.

STEREO 3.5MM MINIATURE PHONE PLUGS

Stereo MINIATURE PHONE PLUG

3.5MM 3 Conductor. Solder terminals, black plastic body with molded in strain relief. Body 3/8" diameter, overall length 2 1/8"

No. 502P - display package of one
No. 502PB - bulk packaged
No. 502GP - display package, gold plated
No. 502GPB - bulk packaged, gold plated
No. 70-017 - gray handle, display pkg. of 2
No. 70-017B - bulk packaged



RIGHT ANGLE STEREO 3.5 mm PLUG

Black plastic body with molded strain relief, solder terminal. Maximum cable O.D - 4.0 mm.



No. 70-097 - right angle, display pkg. of 1
No. 70-097B - right angle, bulk packed

SHIELDED STEREO 3.5 mm PLUG

Handle is nickel plated steel for shielding. Metal spring strain relief.



No. 502M - display pack of 2
No. 502MB - bulk packed

4 Conductor 3.5mm MINIATURE PHONE PLUG & JACKS



70-047

70-086



70-088

No. 70-047 - in-line male, display pkg. of 1
No. 70-047B - in-line male, bulk packaged
No. 70-086 - in-line female, display pkg. of 1
No. 70-086B - in-line female, bulk packaged
No. 70-088 - chassis mt. female, display pkg. of 1
No. 70-088B - chassis mt. female, bulk packed

STEREO 3.5 mm MINIATURE PHONE JACKS

Stereo MINIATURE PHONE JACK

3.5MM, 3 Conductor. Solder terminals, black plastic body with molded-in strain relief. Body 3/8" diameter, overall length 2 1/8"

No. 502V - display package of one
No. 502VB - bulk packaged
No. 70-026 - gray handle, display pkg. of 2
No. 70-026B - bulk packaged



Stereo MINIATURE PHONE JACK

Chassis or PC board mounting. 3.5mm, 3 Conductor. Solder terminals, Completely sealed jack, switching. Mounts in 15/64" hole in panels up to 1/16" thick.



No. 502J - display package of one
No. 502JB - bulk package

Stereo MINIATURE PHONE JACK

Chassis or Panel mounting. 3.5mm, 3 Conductor with solder terminals. Completely sealed jack, non-switching. Mounts in 1/4" hole in panels up to .075" thick. With hardware, attractive knurled nut.

No. 504K - display package of one
No. 504KB - bulk packaged



TWO CONDUCTOR (MONO) MINIATURE PHONE PLUGS

Mono 3.5mm PHONE PLUG

This miniature phone plug has molded-in strain relief. Other specifications are same as for No. 501P shown below. Two black plugs per package.

No. 501PS - package two black
No. 501PSB - bulk packaged
No. 70-015 - gray handle, display pkg. of 2
No. 70-015B - bulk packaged



RIGHT ANGLE MONO 3.5 mm PLUG

Black plastic body with molded strain relief. Solder terminals, Maximum cable O.D. 4.0 mm.

No. 70-095 - display pack of 1
No. 70-095B - bulk packed



Mono 3.5mm PHONE PLUG

Two conductor miniature phone plug. Solder lug terminals. Overall length is 1-5/8" Dimensions are 9/16" x 1/8".



No. 501P - packaged one black and one red
No. 501PB-BK - bulk packaged, black
No. 501PB-RD - bulk packaged, red

SHIELDED MONO 3.5 mm PLUG

Handle is nickel plated steel for shielding. Metal spring strain relief.



No. 115P - display pack of 2
No. 115PB - bulk packed

TWO CONDUCTOR (MONO) MINIATURE PHONE JACKS

TWO CONDUCTOR (MONO) 3.5 mm MINIATURE INLINE PHONE JACK

Molded body (black plastic), solder terminals.



No. 501VS - display package of one
No. 501VSB - bulk packaged
No. 70-024 - gray handle display pkg. of 2
No. 70-024B - bulk packaged

TWO CONDUCTOR (MONO) MINIATURE PHONE JACK

An in-line (or cord mounting) standard 1/8" (3.5mm) miniature phone jack; two conductor monaural. Open circuit (non switching). Black plastic shell, solder connections.



No. 501V - display package of one
No. 501VB - bulk packaged