



# Certificate

**Customer:** Panduit Corporation  
10500 West 167<sup>th</sup> Street  
Orland Park  
Illinois 60467, USA

**Description:** **Panduit Mini-Com<sup>®</sup> TX6<sup>™</sup> PLUS  
Shielded Jack Module**

Part-No.: CJS688TGY

**Applied standards:** ISO/IEC 11801:2002-09  
Information technology – Generic cabling for customer premises  
EN 50173-1: 2002  
Information technology – Generic cabling systems Part 1  
IEC 60603-7-5 / Ed. 1.0 (ACDV 09.2003): Connectors for electronic equipment  
– Part 7-5: Detail specification for 8-way, shielded, free and fixed connectors,  
for Data transmissions with frequencies up to 250 MHz (Cat 6, shielded) - 2003  
TIA/EIA-568-B.2-1 (Addendum No.1 to TIA/EIA-568-B.2) - June 2002  
Transmission Performance Specifications for 4-Pair 100Ω Category 6 Cabling

**Result:** Up to a bandwidth of 250 MHz the sample, meets the limits of the specified standards and regulations and comply with the requirements of the **Category 6** threshold values.

The test results, which were determined in the course of the measurement, refer to the submitted sample. Any future technical modifications of the component are subject to the responsibility of the manufacturer.

This Certificate refers to the comprehensive test report, **no. P1879a-08-E, from March 31<sup>st</sup> 2008** and shall only be applicable in conjunction with the test report.

Bexbach, March 31<sup>st</sup> 2008

Dirk Wilhelm, engineer  
(Chairman of the Managing Board)



GHMT AG  
In der Kolling 13  
D-66450 Bexbach  
Phone: +49 (0) 68 26 / 92 28 – 0  
Fax: +49 (0) 68 26 / 92 28 – 99  
E-Mail: [info@ghmt.de](mailto:info@ghmt.de)  
<http://www.ghmt.de>