


NOTES:

1. MAT'L. - NEOPRENE:
RATING AS REQUIRED TO MEET MIL-R-6855 SPEC.
2. COLOR - BLACK
- Ⓐ 3. PART WEIGHT: 8.7 LBS, PER 100 FT.
4. 60±5 SHORE A DUROMETER RATING
5. TEMPERATURE RANGE OF -40°F (-40°C) TO 200°F (93°C)
6. DIM'S IN [BRACKETS] ARE MILLIMETERS.

S41202_01

									 CORP. TINLEY PARK, ILLINOIS		
01	6/05	JAMB		Ⓐ REMOVED PART WGT. "43.5 lbs PER 500 FT."	12683					MLTEH/SH CUSHION SLEEVING PCSSH-B-CR	
00	5/05	JMMR	EJD	DRAWING RELEASED	12198	SKB	CCH				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								JMMR	EJD	3x	S41202