


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	LENGTH	WEIGHT
Δ DJS1**6	72.0 ± .40 (1828.8 ± 10.2)	.081b / ft (.12g / mm)
DJSP1LG-0	.47 ± .06 (11.9 ± 1.5)	.3291b / 100 pcs (149g)
DJSP1.5LG-0	1.04 ± .06 (26.4 ± 1.5)	.7281b / 100 pcs (331g)
DJSP2LG-0	1.47 ± .06 (37.3 ± 1.5)	1.0261b / 100 pcs (466g)
DJSP3LG-0	2.46 ± .06 (62.5 ± 1.5)	1.7211b / 100 pcs (782g)
DJSP4LG-0	3.44 ± .06 (87.4 ± 1.5)	2.4061b / 100 pcs (1094g)

- NOTES:
 1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGING QUANTITY.
 2. DIMENSIONS IN PARETHESES ARE METRIC.

** = COLOR (SEE CATALOG)

CAD FILENAME/LAYERS D34518_DJS1_CTL_C_01A.prt

PANDUIT CORP. TINLEY PARK, ILLINOIS

DUCT JOINING STRIP (DJS**6)
 CUT TO LENGTH (DJSP*LG-Q)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:
 (.X) : (.XXX) :
 (.XX) : ANGLES :

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN
 IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	DRAWN BY DW	MAT'L:	SCALE	DRAWING NO.	DWG SIZE	
I	8-28-01	JCST	JKG	A. ADDED "DJS**6" REPLACED DRAWING SS-17439	34518-42	JKG	JKG			POLYVINYL CHLORIDE	FULL			
R	4-18-94	DW	CEF	RELEASED TO PRODUCTION	34518-42	CEF	CEF		DATE 4-18-94					
									CHK'D CEF				34518-42	A