



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CPP48HDEWBL	6.15 LB/10 PCS (2788.0 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
  - (1) -48 PORT STAMPING
  - (6) -8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
  - (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS AND FOUR LOCK WASHERS)
  - (1) -SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN PARENTHESIS ARE IN METRIC.



THIS PATCH PANEL WILL ONLY ACCEPT RJ45 COPPER CONNECTORS. FIBER AND AV MODULES WILL NOT FIT CORRECTLY TO ACCEPT THEIR MATING PLUG.

[6.4] DETAIL VIEW OF LABEL AREA

MODEL FILENAME M00741FE_CPP48HDNS_ASSY_00.PRT	SIZE A
DRAWING FILENAME M00741FE_DC_00A.PRT	

MINI-COM 48 PORT HIGH DENSITY MODULAR PATCH PANEL WITH ENHANCED LABELING AREA  
CUSTOMER DRAWING

<p>PANDUIT<sup>TM</sup> CORP. TINLEY PARK, ILL 60477</p> <p>THIRD ANGLE PROJECTION</p> <p>ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.</p> <p>DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±</p>	I.I. NUMBER	N/A
	PRODUCT SPEC	N/A
	WORK INSTRUCTION	N/A
	SCALE	NONE
DRAWN BY JsP	MATERIAL:	PART NO. CPP48HDEWBL
DATE 12-19-05	20 GAGE C.R.S.	DRAWING NO. 00741-118

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	12-19-05	JsP	JsP	RELEASED TO PRODUCTION	00741-118	JsP	JsP	JsP	