


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	LENGTH	WEIGHT
A DJS1**6	72.0 ± 0.40 (1828.8 ± 10.2)	.081b / ft (.12g / mm)
DJSP1LG-0	.47 ± 0.06 (11.9 ± 1.5)	.3291b / 100 pcs (149g)
DJSP1.5LG-0	1.04 ± 0.06 (26.4 ± 1.5)	.7281b / 100 pcs (331g)
DJSP2LG-0	1.47 ± 0.06 (37.3 ± 1.5)	1.0261b / 100 pcs (466g)
DJSP3LG-0	2.46 ± 0.06 (62.5 ± 1.5)	1.7211b / 100 pcs (782g)
DJSP4LG-0	3.44 ± 0.06 (87.4 ± 1.5)	2.4061b / 100 pcs (1094g)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGING QUANTITY.
- DIMENSIONS IN PARETHESES ARE METRIC.

** = COLOR (SEE CATALOG)

CAD FILENAME/LAYERS D34518_DJS1_CTL_C_01A.prt

PANDUIT

TINLEY PARK, ILLINOIS

DUCT JOINING STRIP (DJS**6)
CUT TO LENGTH (DJSP*LG-0)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) :
(.XXX) :
(.XX) :
ANGLES :

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
DW

DATE
4-18-94

CHK'D
CEF

1 8-28-01 JCST JKG A. ADDED "DJS**6"
REPLACED DRAWING SS-17439

R 4-18-94 DW CEF RELEASED TO PRODUCTION

REV DATE BY CHK DESCRIPTION

SCALE FULL

DRAWING NO. 34518-42
DWG A
SIZE

POLYVINYL
CHLORIDE

ECN - R CUST SUP