


Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Part Drawings
  - PDFDOMETOP Bar..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'BT4LH-TL69'

Your search criteria matched only one product, shown below

**BT4LH-TL69**



- Flammability rating of UL94V -0 – indoor use
- Dome -top head features unique patented design with round, smooth edges
- Stainless steel locking barb provides consistent performance, reliability, and infinite adjustability through entire bundle range
- High strength and low thread force
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light -Heavy cross section ties have a straight tip)
- Complementary flame retardant mounts available

|                                   |                                                                                     |
|-----------------------------------|-------------------------------------------------------------------------------------|
| Part Number                       | BT4LH-TL69                                                                          |
| RoHS Compliancy Status            | Compliant                                                                           |
| Part Description                  | Cable Tie, Metal Barb, 14.9"L (378mm), Light-Heavy, Flame Retardant Nylon, Ivory    |
| Product Type                      | Cable Ties                                                                          |
| Material                          | Flame Retardant Nylon 6.6                                                           |
| Color                             | Ivory                                                                               |
| CSA Certified                     | Yes                                                                                 |
| UL Listed (File #E56854)          | No                                                                                  |
| UL Recognized (File #E56854)      | Yes                                                                                 |
| Length (In.)                      | 14.9                                                                                |
| Length (mm)                       | 378                                                                                 |
| Width (In.)                       | 0.275                                                                               |
| Width (mm)                        | 7.0                                                                                 |
| CE Compliant                      | Yes                                                                                 |
| Cross Section                     | Light-Heavy                                                                         |
| Head Height (In.)                 | 0.320                                                                               |
| Head Height (mm)                  | 8.1                                                                                 |
| Head Width (In.)                  | 0.520                                                                               |
| Head Width (mm)                   | 13.2                                                                                |
| Locking Style                     | Locking                                                                             |
| Material Flammability Rating      | V-0                                                                                 |
| Max. Bundle Diameter (In.)        | 4.00                                                                                |
| Max. Bundle Diameter (mm)         | 102                                                                                 |
| Max. Continuous Use Temperature   | 212°F (100°C)                                                                       |
| Min. Bundle Diameter (In.)        | 0.19                                                                                |
| Min. Bundle Diameter (mm)         | 4.8                                                                                 |
| Min. Loop Tensile Strength (Lbs.) | 120                                                                                 |
| Min. Loop Tensile Strength (N)    | 534                                                                                 |
| Plenum Rated                      | No                                                                                  |
| Pricing Description               | Cable Tie, Metal Barb, 14.9"L (378mm), Light-Heavy, Flame Retardant Nylon, Ivory    |
| Thickness (In.)                   | 0.065                                                                               |
| Thickness (mm)                    | 1.7                                                                                 |
| Tool                              | GTH, GS4H, GS4EH, PTH, STH2, ST3EH                                                  |
| Min. Order UOM                    | PC                                                                                  |
| Min. Order Qty.                   | 250                                                                                 |
| BOM Qty. (# of Pkgs.)             | <input type="text" value="0"/>                                                      |
| Add to Favorite Product List      |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.