


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FIBER JACK PLUG  
DUST CAPS REMOVED

MT-RJ CONNECTOR  
DUST CAP REMOVED

NOTES:


1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. FOR LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
3. TESTED TO EIA/TIA 568-B.3.
4. PATCH CORD ROUTING CONFIGURATION A TO B.

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS
F6Z6P-12M*	62.5/125um OR 50/125um MULTIMODE RISER RATED PATCHCORD FIBER JACK PLUG TO MT-RJ	1, 2, 3, 5, & 10 METER
F5Z6P-12M*		

COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE RISER RATED	ORANGE	
CONNECTORS	OPI-JACK PLUG	ELECTRIC IVORY	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS
F6LZ6P-12M*	62.5/125um OR 50/125um MULTIMODE LS-ZH PATCHCORD FIBER JACK PLUG TO MT-RJ	1, 2, 3, 5, & 10 METER
F5LZ6P-12M*		

COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE LOW SMOKE-ZERO HALOGEN	ORANGE	
CONNECTORS	OPI-JACK PLUG	ELECTRIC IVORY	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

PART NUMBER		F * Z6P - 12M * , F * LZ6P - 12M *	
TITLE			
FIBER OPTIC PATCH CORD FIBER JACK PLUG TO MT-RJ CONFIGURATION			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02412BT/01	
DATASET FILE NAME		M02412BT_DC/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN ( mm )			MATERIAL:
.X ±	.XXX ±	THIRD ANGLE PROJECTION	
.XX ±	ANGLES ±		DRAWING NUMBER:
			02412-08
DRAWN BY	DATE	CHK	SCALE
MC	11-07-05	RAF	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	2/22/16	JSP	WJM	RWB	A. UPDATED DRAWING TITLE BLOCK.	02412-08

D10100DA/14