


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	"A" (IN.) MIN.	"B" (IN.) ±0.062	"C" +/- .062 (IN.)	MATERIAL	COLOR	PART NO.	"A" (IN.) MIN.	"B" (IN.) ±.062	"C" +/- .062 (IN.)	MATERIAL	COLOR
T100X000YK1	1200	1.00	0.125	GMV4-C	CLEAR	T200X000VS1Y	1200	2.00	0.125	GMV14	GREEN
T200X000VR1Y	1200	2.00	0.125	GMV14	BROWN	T200X000VU1Y	1200	2.00	0.125	GMV14	ORANGE
T200X000YK1	1200	2.00	0.125	GMV4-C	CLEAR	T200X000VW1Y	1200	2.00	0.125	GMV14	RED
T225X000YK1	1200	2.25	0.125	GMV4-C	CLEAR	T200X000VX1Y	1200	2.00	0.125	GMV14	YELLOW
T400X000VR1Y	1200	4.00	0.125	GMV14	BROWN	T400X000VY1Y	1200	4.00	0.125	GMV15	BLACK
T400X000YK1	1200	4.00	0.125	GMV4-C	CLEAR	T400X000VT1Y	1200	4.00	0.125	GMV14	GRAY
T425X000YK1	1200	4.25	0.125	GMV4-C	CLEAR	T400X000VV1Y	1200	4.00	0.125	GMV15	PURPLE
T100X000VP1Y	1200	1.00	0.125	GMV14	WHITE	T400X000VP1Y	1200	4.00	0.125	GMV14	WHITE
T100X000VU1Y	1200	1.00	0.125	GMV14	ORANGE	T400X000VQ1Y	1200	4.00	0.125	GMV15	BLUE
T100X000VX1Y	1200	1.00	0.125	GMV14	YELLOW	T400X000VS1Y	1200	4.00	0.125	GMV14	GREEN
T100X000VQ1Y	1200	1.00	0.125	GMV15	BLUE	T400X000VU1Y	1200	4.00	0.125	GMV14	ORANGE
T100X000VS1Y	1200	1.00	0.125	GMV14	GREEN	T400X000VW1Y	1200	4.00	0.125	GMV14	RED
T100X000VW1Y	1200	1.00	0.125	GMV14	RED	T400X000VX1Y	1200	4.00	0.125	GMV14	YELLOW
T100X000VY1Y	1200	1.00	0.125	GMV15	BLACK	T200X000Y2T	180	2.00	0.125	GMV4-HT	WHITE/GREEN
T200X000VY1Y	1200	2.00	0.125	GMV15	BLACK	T400X000Y2T	180	4.00	0.125	GMV4-HT	WHITE/GREEN
T200X000VT1Y	1200	2.00	0.125	GMV14	GRAY						
T200X000VV1Y	1200	2.00	0.125	GMV15	PURPLE						
T200X000VP1Y	1200	2.00	0.125	GMV14	WHITE						
T200X000VQ1Y	1200	2.00	0.125	GMV15	BLUE						



NOTES:  
1. RESIN RIBBON  
RECOMMENDED.

CAD FILENAME/LAYERS		100472ER-DC-C10274/11H	
<h1>PANDUIT</h1> CORP. TINLEY PARK, ILLINOIS			
<b>THERMAL TRANSFER CONTINUOUS TAPES</b>			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12    (.XXX) ± .025 (.XX) ± .062    ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
7	6/21/12	RVU	CHANGE GMV15 INSTEAD OF GMV14 (for the black and purple parts only).
6	5/7/12	RVU	GMV14 CHANGES TO GMV15.
REV	DATE	BY	CHK
DESCRIPTION		ECN - R	CUST SUP
DRAWN BY		MAT'L:	
DATE		SEE TABLE	
CHK'D		SCALE	
		NTS	
		DRAWING NO.	
		C10274	
		DWG SIZE	
		A	