



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT PART NUMBER | PACKAGE QUANTITY | MAX BUNDLE DIA [mm] | LENGTH "L" +/- .2 [5] | MARKING "XXX SS" |
|---------------------|------------------|-----------------------|-------------------------|------------------|
| MS4W75T30-Q6 | 25 | 4" [102] | 20.2" [513] | 316 SS |
| MS6W75T30-Q6 | 25 | 6" [152] | 26.5" [673] | 316 SS |
| MS8W75T30-Q6 | 25 | 8" [203] | 32.7" [831] | 316 SS |
| MS10W75T30-Q6 | 25 | 10" [254] | 39.0" [991] | 316 SS |
| MS12W75T30-Q6 | 25 | 12" [305] | 44.7" [1135] | 316 SS |
| MS14W75T30-Q6 | 25 | 14" [356] | 50.1" [1273] | 316 SS |



NOTES:

1. APPLICATION TOOLS: BT75SDT
2. ALL DIMENSIONS IN BRACKETS [] ARE MILLIMETERS
3. MATERIAL: 316 STAINLESS STEEL
4. MAX BUNDLE SIZE FOR SINGLE LOOP APPLICATIONS
BUNDLE SIZE IS HALVED FOR DOUBLE LOOP APPLICATIONS.

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN | TITLE | ITEM REVISION NAME | DATASET FILE NAME | MATERIAL: | DRAWING NUMBER: |
|-----|------|----|-----|-----|-------------|-----|--|--------------------|-------------------|--|-----------------|
| | | | | | | | DISCRETE LENGTH TIE .750" [19.05] WIDE | | | | |
| | | | | | | | CUSTOMER DRAWING | | | | |
| | | | | | | | | N41311BS/02 | | | |
| | | | | | | | | | N41311BS_DC/02A | | |
| | | | | | | | | | | UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | SEE NOTES |
| | | | | | | | | | | .x ± N/A .xx ± N/A | |
| | | | | | | | | | | .xxx ± N/A ANGLES ± N/A | |
| | | | | | | | | | | THIRD ANGLE PROJECTION | N41311BS_DC |
| | | | | | | | | | | | SHT 1 OF 1 |
| | | | | | | | | | | | A |