


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



P/N	MATERIAL	COLOR	"A" +/- .04	"B" +/- .04	"D" +/- .04	"E" +/- .04	LABEL PER ROWS	ROWS PER FANFOLD	WEB WIDTH "F" +/- .062	STANDARD PACKAGE QTY.
PDL-86	GMT	WHITE	1.50 (38.1)	0.25 (6.4)	1.83 (46.5)	0.33 (8.5)	4	36	8.00 (203.2)	5000
PDL-87	GMY	WHITE	1.50 (38.1)	0.25 (6.4)	1.83 (46.5)	0.33 (8.5)	4	36	8.00 (203.2)	5000
PDL-89	GMP	WHITE	0.50 (12.7)	0.75 (19.1)	0.60 (15.2)	1.00 (25.4)	14	12	9.30 (236.2)	5000
PDL-92	GMP	WHITE	0.90 (22.9)	0.25 (6.4)	1.00 (25.4)	0.33 (8.5)	8	36	8.90 (226.1)	5000
PDL-93	GMC	WHITE	0.90 (22.9)	0.25 (6.4)	1.00 (25.4)	0.33 (8.5)	8	36	8.90 (226.1)	5000
PDL-94	GMY	WHITE	0.90 (22.9)	0.25 (6.4)	1.00 (25.4)	0.33 (8.5)	8	36	8.90 (226.1)	5000
PDL-94-10	GMY	WHITE	0.90 (22.9)	0.25 (6.4)	1.00 (25.4)	0.33 (8.5)	8	36	8.90 (226.1)	10000
PDL-99	GMT	WHITE	1.00 (25.4)	0.50 (12.7)	1.10 (27.9)	0.67 (16.9)	7	18	8.60 (218.4)	5000
PDL-110	GMT	WHITE	2.00 (50.8)	0.38 (9.5)	2.10 (53.4)	0.50 (12.7)	3	24	7.20 (182.9)	5000
PDL-111	GMY	WHITE	2.00 (50.8)	0.38 (9.5)	2.10 (53.4)	0.50 (12.7)	3	24	7.20 (182.9)	5000
PDL-112	GMP	WHITE	2.00 (50.8)	0.38 (9.5)	2.10 (53.4)	0.50 (12.7)	3	24	7.20 (182.9)	5000
PDL-113	GMV	WHITE	2.00 (50.8)	0.38 (9.5)	2.10 (53.4)	0.50 (12.7)	3	24	7.20 (182.9)	5000



* PDL-86
* PDL-87

NOTES:
1. MILLIMETERS ARE IN ().

CAD FILENAME/LAYERS		100619GK_DC_C10003/03C	
CORP. TINLEY PARK, ILLINOIS			
CUSTOMER DRAWING PDL-** COMPUTER PRINTABLE LABELS			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .025 (.XX) ± .062 ANGLES		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU		MAT'L:	
DATE 3-22-01		AS NOTED	
CHK'D		SCALE 1/2	
REV		DRAWING NO. C10003	
DATE		DWG A SIZE	
BY			
CHK			

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
I	8/24/09	RVU		CHG. FORMAT A TO B. ADD TOLERANCE, .12, .062, .025. ADD +/- .04.	5834		R	
R	5-16-06	RVU		DRAWING RELEASE	4484		R	