


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

P/N	MATERIAL	COLOR	A	B	C	E	LABEL PER ROWS	ROWS PER FANFOLD	WEB WIDTH F in. (mm)	STANDARD PACKAGE QTY.	REF. TO MFG. DWG.
PDL-6	GMV3	WHITE	1.00 (25.4)	3.94 (100.1)	1.00 (25.4)	4.00 (101.6)	8	3	9.00 (228.6)	1000	A62019
PDL-6-10	GMV3	WHITE	1.00 (25.4)	3.94 (100.1)	1.00 (25.4)	4.00 (101.6)	8	3	9.00 (228.6)	10000	A62019
PDL-6-2.5	GMV3	WHITE	1.00 (25.4)	3.94 (100.1)	1.00 (25.4)	4.00 (101.6)	8	3	9.00 (228.6)	2500	A62019
PDL-6VF	GMVF	CLEAR	1.00 (25.4)	3.94 (100.1)	1.00 (25.4)	4.00 (101.6)	8	3	9.00 (228.6)	5000	A62082
PDL-7	GMV3	WHITE	2.00 (50.8)	3.94 (100.1)	1.00 (25.4)	4.00 (101.6)	4	3	9.00 (228.6)	1000	A62021
PDL-7-10	GMV3	WHITE	2.00 (50.8)	3.94 (100.1)	1.00 (25.4)	4.00 (101.6)	4	3	9.00 (228.6)	10000	A62021
PDL-168	GMV3	WHITE	0.36 (9.14)	0.94 (23.8)	0.38 (9.5)	1.00 (25.4)	22	12	7.94 (201.68)	5000	A62096
PDL-239	GMV3	WHITE	0.30 (7.6)	0.75 (19.1)	0.38 (9.5)	1.00 (25.4)	16	12	5.80 (147.3)	5000	A62123
PDL-242	GMT1	WHITE	0.50 (12.7)	0.94 (23.8)	0.38 (9.5)	1.00 (25.4)	16	12	9.00 (228.6)	5000	A62125
PDL-243	GMV3	WHITE	0.50 (12.7)	0.94 (23.8)	0.38 (9.5)	1.00 (25.4)	16	12	9.00 (228.6)	5000	A62126
PDL-246	GMT1	WHITE	0.80 (20.3)	0.94 (23.8)	0.38 (9.5)	1.00 (25.4)	10	12	9.00 (228.6)	5000	A62128
PDL-247	GMV3	WHITE	0.80 (20.3)	0.94 (23.8)	0.38 (9.5)	1.00 (25.4)	10	12	9.00 (228.6)	5000	A62130
PDL-248	GMT1	WHITE	1.00 (25.4)	0.75 (19.1)	0.38 (9.5)	1.00 (25.4)	8	12	9.00 (228.6)	5000	A62131
PDL-249	GMV3	WHITE	1.00 (25.4)	0.75 (19.1)	0.38 (9.5)	1.00 (25.4)	8	12	9.00 (228.6)	5000	A62132
PDL-249-1	GMV3	WHITE	1.00 (25.4)	0.75 (19.1)	0.38 (9.5)	1.00 (25.4)	8	12	9.00 (228.6)	1000	A62132
PDL-251	GMV3	WHITE	1.00 (25.4)	0.94 (23.8)	0.38 (9.5)	1.00 (25.4)	8	12	9.00 (228.6)	5000	A62134

NOTES:

1. ALL LABELS TO BE DIE-CUT AND EQUALLY SPACED AS SHOWN.
2. REF. MFG. DWG. SEE TABLE.



REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
R	6-13-06	RVU		DRAWING RELEASE	4484	R		

CAD FILENAME/LAYERS		I00619MN_C10013_PDL_00.PRT	
PDL SELF-LAMINATING LABELS BY SIZE CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY RVU	MAT'L: SEE TABLE	SCALE NTS	
DATE 5-10-01	CHK'D	DRAWING NO. C10013	DWG SIZE B