



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	STYLE	MATERIAL	"A" +/- .062	"B" +/- .062
PDP-6	A	GMH1 8.0 MIL WHITE POLYESTER/ POLYCARBONATE	2.0 [50.8]	0.50 [12.7]
PDP-21	B	GMH1 8.5 MIL., WHITE POLYESTER GMY1	3.0 [76.2]	1.0 [25.4]
PDP-29	A	GMV9 10 MIL, WHITE VINYL	2.0 [50.8]	0.75 [19.1]

NOTES:
1. MILLIMETER ARE IN [].

STYLE A
WITH DETACHABLE PINFEED STRIP AND A PRE-CUT MOUNTING HOLE FOR STANDARD CROSS SECTION CABLE TIES



STYLE B
USES PINFEED AS MOUNTING HOLE FOR INTERMEDIATED CROSS SECTION CABLE TIES

CAD FILENAME/LAYERS 1002811V-DC-C10718/03A

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
PDP-6, PDP-21 & PDP-29
DATA PLATE LABELS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (.XXX) ± .025
(.XX) ± .062 ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
RVU

MAT'L:

SCALE
NTS

DATE
3/29/10

SEE TABLE

DRAWING NO.

C10822

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	3/29/10	RVU		DRAWING RELEASE.	5999	R		