

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'CCH75-S10-C0'

Your search criteria matched only one product, shown below

**CCH75-S10-C0**



- Durable nylon cable clamps

Part Number	CCH75S10-C0
RoHS Compliancy Status	Compliant
Part Description	Heavy Duty Fixed Diameter Cable Clamp
Product Type	Mounting Device
Material	Weather Resistant Nylon 6.6
Color	Black
UL Recognized	E136577
Diameter (In.)	.20
Diameter (mm)	5.1
Width (In.)	.50
Width (mm)	12.7
Bundle Offset (mm)	19.8
Bundle Offset (In.)	.78
CE Compliant	No
CE Marking	No
Environment	Indoors/Outdoors
Flammability Rating	UL94 V-2
Max. Bundle Diameter (In.)	.75
Max. Bundle Diameter (mm)	19.1
Mounting Method	#10 (M5) Screw
Pricing Description	Fixed Dia Clamp, .75" (19.1mm) Bundle, #10 Screw (M5), BL
Screw Size Metric	M5
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.