

**Search Results**

Evaluate


- FAQ's
- Product Bulletins
- PDFObsolete and ..
- Selection Guides
- PDFConvenience..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DNF18-250-E'

Your search criteria matched only one product, shown below

**DNF18-250-E**



- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
- UL Flammability UL 94V -2/HB, maximum insulation temperature 194°F (90°C)
- UL and CSA rated up to 300 V per UL 310, where applicable
- ‡UL and CSA approved tooling/product combinations.

Part Number	DNF18250-E
RoHS Compliancy Status	Compliant
Part Description	Female Disconnect, nylon barrel insulated, funnel entry, 22- 18 AWG, .250 x .032 tab size.
Product Type	Disconnects
CSA Certified	Yes
UL Listed	Yes
Height (In.)	0.12
Height (mm)	3.0
Length (In.)	0.81
Length (mm)	20.6
Width (In.)	0.29
Width (mm)	7.4
CE Compliant	No
Insulation	Nylon
Max. Ins.	0.138
Max. Ins. (mm)	3.5
Panduit Color Code	Red
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Tab Size (In.)	0.250 x 0.032
Tab Size (mm)	6.3 x 0.8
Temperature Rating	194 Degrees Fahrenheit (90 Degrees Celsius)
Tool	CT-600-A‡, CT-1550, CT-1551, CT-2500
Wire Range	22 – 18 AWG
Wire Range (mm <sup>2</sup> )	0.5 – 1.0
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.