

Search Results

- Evaluate
  - FAQ's
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'LCCX4/0-14B-X'

Your search criteria matched only one product, shown below

**LCCX4/0-14B-X**



For Use with Flexible, Extra-Flexible, and Code Stranded Copper Conductors

- Can be used with code conductor and flex conductor class: G, H, I, K, M and Diesel Locomotive
- Long barrel maximizes number of crimps and provides premium wire pull -out strength and electrical performance
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV\*\* and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- Meets J-STD-607-A and TIA-942 requirements for network systems grounding applications
- Available with NEMA hole sizes and spacing

Note: These flex conductor lugs are manufactured for use with AWG wire only.

Part Number	LCCX4/0-14B-X
RoHS Compliancy Status	Compliant
Part Description	Flex lug, long barrel, 4/0 AWG, 2hole, 1/4" stud holes, .75 hole spacing.
CSA Certified	Yes
UL Listed	Yes
Length (In.)	4.07
Length (mm)	103.4
Class G,H, I, K, M	4/0 AWG
Diesel Locomotive	4/0 AWG
Stud Hole Size (In.)	1/4
Stud Hole Spacing (In.)	0.75
Tongue Width (In.)	1.19
Barrel Length (In.)	2.24
Angle	Straight
Barrel Length (mm)	56.9
CE Compliant	No
Figure No.	1
Panduit Color Code	Purple
PANDUIT Die Color & Die No.	Purple P54
Panduit Die Index No.	P54
Pricing Description	Copper Comp. Lug, 2 Hole, 4/0 AWG Flex, 1/4" (6.4mm) Stud, .75" (19.1mm) Hole Spacing
Stud Hole Size (mm)	6.4
Tongue Thickness	0.16
Tongue Type	Standard
Tongue Width (mm)	30.2
Tool	CT-930, CT-2931
Wire Range (mm <sup>2</sup> )	120
Wire Strip Length (In.)	2 5/16
Wire Strip Length (mm)	59.0
Min. Order Qty.	1
Burndy Die Index No.	15
T&B Die Index No.	54
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.