

Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Catalog Cut Sheet
  - PDFGUBC5006 Pr
  - Part Drawings
  - PDFAuxiliary Ca ..
  - Specification Sheets
  - PDFAuxiliary Ca ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor
- Install & Maintain
  - Installation Instructions
  - PDFGround Auxil ..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'GACBJ68U'

Your search criteria matched only one product, shown below

**GACBJ68U**



- Bonds ladder rack and Panduit ® Wyr-Grid™ System sections together without drilling holes
- Supports grounding conductors in the telecommunications room, allows separation of grounding conductors from other cables
- Holds up to four conductors in sizes up to 750 kcmil
- Bonds to all 1" and 2" ladder rack rails
- Paint piercing teeth provide electrical continuity between cable pathway sections while minimizing debris
- Front and back mounting screw options allow easy installation and visual inspection
- GACB-2 and GACB-3 can be mounted above or below the cable pathway system for flexibility
- Brackets Meet TIA-607-B

Part Number	GACBJ68U
RoHS Compliancy Status	Compliant
Part Description	Auxiliary cable bracket jumper for bonding pathway sections; #6 AWG (16mm <sup>2</sup> ); 8.0" (203mm) length; factory terminated on both ends with straight, two-hole, long barrel compression lugs; provided with .16 oz. (5cc) of antioxidant and four mounting screws.
CE Compliant	No
Pricing Description	Auxiliary Cable Bracket Jumper, #6 AWG (16mm <sup>2</sup> ), 8.0" (203mm) length
Min. Order UOM	KT
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.