


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	MIN. LOOP * TENSILE lbs. (N)	CROSS SECTION
	MIN. in (mm)	MAX. in (mm)							
HLT2I	.25 (6.4)	1.91 (48.5)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	8.0 (203)	40 (178)	INTERMEDIATE
HLT3I	.25 (6.4)	3.18 (80.6)	.100 (2.5)	.50 (12.7)	1.50 (38.1)	1.00 (25.4)	12.0 (305)	40 (178)	INTERMEDIATE

NOTES:

- 1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
- \* 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

							CAD FILENAME/LAYERS		
							DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS		
							SS_26938_04.PRT		
							PANDUIT CORP. TINLEY PARK, ILLINOIS		
							TAK-TY™ HOOK & LOOP CABLE TIES HLT SERIES		
4	1/8/99	KT		(B) ADDED REF. TO SLOT AND CUT-THRU DIM.	26938	4			
3	10/22/98	KT	HVP	(A) TAK-TY™ WAS VELCRO®	26938	3			
2	01/18/95	KT	HVP	GENERAL REVISIONS (SEE ECN)	26938	2			
1	01/06/95	KT	JAR	GENERAL REVISIONS (SEE ECN)	26938	1			
R	11/28/94	KT	HVP	DRAWING RELEASED	26938	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	
							DRAWN BY KET	MAT'L:	SCALE NONE
							DATE 11/28/94	POLYETHYLENE HOOK/ NYLON KNIT LOOP	DRAWING NO.
							CHK'D HVP		SS-26938
									DWG SIZE A