

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'HSTT05-48-Q10'

Your search criteria matched only one product, shown below

HSTT05-48-Q10



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
 - Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
- For clear, add "C" to end of part number package suffix (Example HSTT05 -48-QC). Contact customer service for additional color information.

Meets Mil Spec AMS-DTL-23053/5 Class 1(Colors), Class 2 (Clear)

Part Number	HSTT05-48-Q10
RoHS Compliancy Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink
Material	Flame retardant polyolefin cross-linked except clear
Color	White
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 1
UL Recognized	E122770
Length (ft.)	4
Length (m)	1.2
CE Compliant	No
CE Marking	No
Flammability Rating	Flame Retardant
Max. Recovered I.D. (In.)	.023
Max. Recovered I.D. (mm)	.6
Min. Expanded I.D. (In.)	.046
Min. Expanded I.D. (mm)	1.2
Nominal Diameter (In.)	.046
Nominal Diameter (mm)	1.2
Nominal Diameter / Size	.046
Nominal Recovered Wall Thickness (In.)	.016
Nominal Recovered Wall Thickness (mm)	.4
Pricing Description	Heat Shrink Thin, .05"(1.2mm) Dia, White
Shrink Ratio	2:1
Temperature Range	-67°F to 275°F (-55°C to 135°C)
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.