

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) Search Tips

 Text Search: 'HSTT19-48-Q45'

Your search criteria matched only one product, shown below


HSTT19-48-Q45



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT05 -48-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1(Colors), Class 2 (Clear)

Part Number	HSTT1948-Q45
RoHS Compliance Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink
Material	Flame retardant polyolefin cross-linked except clear
Color	Yellow/Green
CSA Certified	Yes
Military Specification	AMS-DTL-23053/5 Class 1
UL Recognized	E122770
Length (ft.)	4
Length (m)	1.2
CE Compliant	No
CE Marking	No
Flammability Rating	Flame Retardant
Max. Recovered I.D. (In.)	.093
Max. Recovered I.D. (mm)	2.4
Min. Expanded I.D. (In.)	.187
Min. Expanded I.D. (mm)	4.8
Nominal Diameter / Size	.187
Nominal Recovered Wall Thickness (In.)	.020
Nominal Recovered Wall Thickness (mm)	.5
Pricing Description	Heat Shrink Thin, .19"(4.8mm) Dia, Yellow/Green
Shrink Ratio	2:1
Temperature Range	-67°F to 275°F (-55°C to 135°C)
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.