



support | locate distributor | about panduit | c

World Leader in Network and Electrical Solutions

HOME | SOLUTIONS | RESOURCES | PRODUCTS | SERVICES | LEARNING

SEARCH

Current refinements (click to remove)

Region **USA** Product Family **HSTTV Heat Shrink on Bulk Reels** Text Search: 'HSTTV50-T'

Your search criteria matched only one product, shown below.



Evaluate, Design & Install
Product: Flexible Polyolefin VW-1 DRY-SHRINK™ Heat Shrink Tubing in Bulk Reels

- For dry locations
- Highly flame retardant Meets UL VW-1 Rating
- Fast Shrink Time
- Material Type: Highly Flexible Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 257°F (-55°C to 125°C)
- Voltage: 600V
- UL VW-1 Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 3

Part Number:	HSTTV50-T
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink (UL224 VW-1)
Material:	Polyolefin cross-linked
Color:	Black
CSA Certified:	Yes
Military Specification:	AMS-DTL-23053/5 Class 3
UL Recognized:	E122770
Length (ft.):	200
Length (m):	61.0
Flammability Rating:	UL224 VW-1
Max. Recovered I.D. (In.):	.250
Max. Recovered I.D. (mm):	6.4
Min. Expanded I.D. (In.):	.500
Min. Expanded I.D. (mm):	12.7
Nominal Diameter / Size:	1/2
Nominal Recovered Wall Thickness (In.):	.025
Nominal Recovered Wall Thickness (mm):	.6
Shrink Ratio:	2:1
Temperature Range:	-67°F to 257°F (-55°C to 125°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.