

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'HSTTV50-48-5'

Your search criteria matched only one product, shown below

### HSTTV50-48-5



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
  - Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
  - Available in various colors for permanent, cost effective color coding
- Meets Mil Spec AMS-DTL-23053/5 Class 3.

▪ Part Number	HSTTV50-48-5
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Thin Wall Polyolefin Heat Shrink (UL224 VW1)
▪ Material	Highly flame retardant polyolefin cross-linked**
▪ Color	Black
▪ CSA Certified	Yes
▪ Military Specification	AMS-DTL-23053/5 Class 3
▪ UL Recognized	E122770
▪ Length (ft.)	4
▪ Length (m)	1.2
▪ CE Compliant	No
▪ CE Marking	No
▪ Flammability Rating	UL224 VW-1
▪ Max. Recovered I.D. (In.)	.250
▪ Max. Recovered I.D. (mm)	6.4
▪ Min. Expanded I.D. (In.)	.500
▪ Min. Expanded I.D. (mm)	12.7
▪ Nominal Diameter (In.)	.500
▪ Nominal Diameter (mm)	12.7
▪ Nominal Recovered Wall Thickness (In.)	.025
▪ Nominal Recovered Wall Thickness (mm)	0.6
▪ Pricing Description	Heat Shrink Thin VW1, .50"(12.7mm)Dia, Black
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F to 257°F (-55°C to 125°C)
▪ Min. Order UOM	PC
▪ Min. Order Qty.	5
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.