

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

Material	High Conductivity Seamless Copper Tube		
Plating	Electro-Tin 2/0 AWG Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric 1-1/16 in. 5/16 in.		
Wire Size			
Wire Type			
Wire Strip Length			
Stud Size			
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.		
UL Temperature Rating	90°C		
C.S.A Certified Wire Connector	Yes		
Panduit Color Code on Barrel	BLACK		
Panduit Die Index No. on Barrel	P45		
Alternate Industry Die Index No. () on Barrel	(13)		









						PAROUIT CORP. TINLEY PARK, ILLINOIS
						LCA2/0-56-X Copper Lug - One-Hole, Standard Barrel
00	9/02	SAB	DRL	RELEASED	10318	Copper Lug - One-Hole, Standard Barrel
REV	DATE	BY	СНК	DESCRIPTION	ECN	SCALE N/A DRAWING NO / CAD FILE LCA2_0-56-CUST