

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDF Copper, Stan..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'LCAXN4/0-56-X'


Your search criteria matched only one product, shown below

LCAXN4/0-56-X



For Use with Flexible Copper Conductors

- Narrow tongue width for limited space applications
- Can be used with flex conductor class: Diesel Locomotive
- Generously beveled wire entry prevents bent back strands when inserting conductor into barrel
- Color-coded barrels marked with Panduit and specified competitor die index numbers for proper crimp die selection
- Inspection window to visually assure full conductor insertion
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV** and temperature rated to 90°C when crimped with Panduit and specified competitor crimping tools and dies

Part Number	LCAXN4/0-56-X
RoHS Compliancy Status	Compliant
Part Description	Flex conductor, one hole, standard barrel narrow tongue lug with inspection window.
Material	Tin-Plated Copper
CSA Certified	Yes
UL Listed	Yes
Length (In.)	2.55
Length (mm)	64.8
Class G,H, I, K, M	4/0
Copper Conductor Size	4/0
Diesel Locomotive	4/0
Stud Hole Size (In.)	5/16
Tongue Width (In.)	0.81
Barrel Length (In.)	1.03
Angle	Straight
Barrel Length (mm)	26.2
Panduit Color Code	Purple
Panduit Die Index No.	P54
Pricing Description	Copper Compression Lug, 1 Hole, 4/0 AWG, Narrow Tongue, 5/16" (7.9mm) Stud
Stud Hole Size (mm)	7.9
Tongue Thickness	0.20
Tongue Type	Narrow
Tongue Width (mm)	20.6
Wire Strip Length (In.)	1 1/16
Wire Strip Length (mm)	75.0
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	15
T&B Die Index No.	54
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.