

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFPD Raceway
 - DWG-PD Raceway
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor
- Install & Maintain
 - Installation Instructions
 - PDFPAN-WAY Type ..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PD6IW6-A'

Your search criteria matched only one product, shown below

PD6IW6-A



Pan-Way® Type PD Surface Raceway is a single channel raceway system to route, protect and conceal power, data, voice, or video cabling.

- UL & CSA rated 600V; meets UL5A and CSA C22.2 No. 62.1 -03 standards
- Textured Finish
- Tamper resistant latch design
- Raceway Base and Cover are packaged together
- FT-4 Rated for Canada

For actual product color please refer to the Surface Raceway Color Chart located in selection guides.

Part Number	PD6IW6A
RoHS Compliancy Status	Compliant
Part Description	Raceway Base and Cover packaged together. Raceway Base with pre-applied adhesive backing to speed installation.
Product Type	Power Rated Raceway
Material	PVC
Color	Off White
CSA Certified	Yes
UL Listed	Yes
Height (In.)	0.48
Length (ft.)	6
Length (In.)	72.00
Width (In.)	1.29
Adhesive Backed	Yes
CE Compliant	No
Channel Type	Single-Channel
Inside Diameter (In.)	(A = 0.33in ²)
Mounting	Adhesive
Pricing Description	PD6 Power Rated, 2piece Single Channel Raceway with Adh. 6ft.
Product Length	6'
Product Size	6
Raceway Size	1.33" x .46"
Min. Order UOM	FT
Min. Order Qty.	6
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.