



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL



ST-100

Self-Adjusting Wire and Cable Cutting and Stripping tool. Strips and cuts #32 AWG – 5 AWG (0.03 – 16mm²) wire, with adjustable stripping length from 3.0-21mm. The tool is designed to prevent damage or fanning of conductors, and features an ergonomic lightweight design for easy mechanical action and less operator fatigue, with easy blade storage in the retractable handle cover.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Color	Black/Gray
Length In (mm)	7.95 (202.0)
Weight lbs (kg)	0.43 (0.2)
Width In (mm)	0.90 (23.0)
Application	Cutting of stranded wire with PVC insulation
Overall Height (In.)	4.5
Overall Height (mm)	114.0
Part Features	<ul style="list-style-type: none"> • Strips and cuts #32-5AWG (0.03-16mm²) wire • Adjustable stripping length from 3.0-21mm • Designed to prevent damage or fanning of conductors • No tools required to change the stripping blades • Ergonomic Lightweight design for easy mechanical action and less operator fatigue • Easy blade storage in retractable handle cover
Tool Type	Electrical
Wire Range In. (mm ²)	32 - 5 AWG (0.03 - 16.0)
RoHS Compliancy Status	RoHS directive is not applicable
Min. Order Qty.	1