




All Products ▾ Solutions ▾ Support ▾

[Home](#) / [Products](#) / [Wire Termination](#) / [Crimpers, Cutters, Strippers & Accessories](#) / [Crimping Tools, Pumps & Accessories](#) / [CD-2001-500-SET](#)



CD-2001-500-SET

CD-2001 Crimp Dies

Crimp dies for CT-3001 tool, 500 kcmil.



Specifications

Panduit Die Index Number	Brown P87
For Use With	CT-3001/ST and CT-3001/CCP Crimping Tool to Crimp 500 kcmil Copper Code, 240mm ² Class 2r Metric Copper Conductor

Part Features	Color coded to connector, premium crimp, embosses die number
RoHS Compliancy Status	RoHS directive is not applicable
Min. Order Qty.	1

Packaging Details

UPC	07498307242
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.1309

Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000



Related Products



CT-1550

Crimps most Panduit #22 – 10 AWG nylon and vinyl insulated terminals, splices, and disconnects. The tool has the red/blue pocket closest to the pivot which provides a reduced crimp effort for those who make red/blue terminations.



CT-2931/ST

The Panduit® BlackFin® Crimping Tool crimps with just the touch of a button. Dies even change out quickly and easily thanks to a 355-degree rotating open C-crimp head. The crimp tool has a force of 12 tons and crimps #8 AWG – 750 kcmil copper code, #8 AWG – 535 kcmil copper flex, #6 AWG - 600 kcmil aluminum, 10mm² – 400mm² copper class 2 metric, 10mm² – 300mm² copper class 5f and 6f metric, #10 AWG – 500 kcmil ferrules and #6 AWG - 250 kcmil copper code Direct Burial Grounding connectors. Includes battery powered crimping tool with two 3.0 Ah Li-ion battery cartridges, 120 V charger with USA Type A plug, carrying case and a shoulder strap. Crimp dies sold separately.



CT-3001/ST

Introducing the Panduit® BlackFin® 3-in-1 in-line Lithium-ion Hydraulic Crimp Tool. Adapters and dies change out quickly and easily thanks to a 355-degree rotating flip-top crimp head. The crimp tool has a force of 6.7 tons and crimps Panduit copper lugs and splices for #8 AWG - 600 kcmil Code, #8 AWG -373 kcmil flex, 10mm² - 240 mm² Class 2r and 10mm² - 95mm² Class 5f and 6f metric, #6 AWG - 350 kcmil aluminum lugs and splices. Copper CTAPF taps up to 4/0 AWG copper CTAP taps up to #2 AWG. Includes CD-3001/ST-DA die adapter for CD-2001 dies, two 3.0 Ah 18 V batteries, 120 V battery charger with North American Type A plug and plastic carrying case. For use with Panduit CD-2001, KC22 and KA22 dies sold separately.



Email Support

Email support available
24/7



800-777-3300

Monday through Thursday
7:00 am-6:30 pm CST
Friday 7:00 am-6:00 pm
CST



Where to Buy

Find a Panduit Distributor
or Partner

ABOUT US

Research and Development

Media Resources

World Headquarters

Awards

Partner Ecosystem

Panduit Code of Conduct

CAREERS AT PANDUIT

THE HUB – PARTNER PORTAL

PRODUCT REGISTRATION

PANDUIT CONNECTIONS BLOG



GET OUR CATALOG

Download the PDF or request a copy be mailed to you.

Which catalog would you like? ▼

▶ **DOWNLOAD** ▶ **REQUEST COPY**

