

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDFDISCOGRIP Fe ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'DPF18-206FIB-C'

Your search criteria matched only one product, shown below

DPF18-206FIB-C



- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
 - Premium nylon insulation retains its shape when crimped and provides a tight grip around the wire insulation for maximum strain relief
 - Fully insulated design provides protection from electrical shorts
 - Internal wire stop assures proper length of insertion into terminal barrel, providing a higher quality connection
 - Disconnects with restricted insulation (Type DPF -FIBR) provide a superior connection in applications requiring the use of extremely thin 22 – 18 AWG wire insulation
 - UL and CSA rated up to 600 V per UL 310
- ‡UL and CSA approved tooling/product combinations.

Part Number	DPF18206FIB-C
RoHS Compliancy Status	Compliant
Part Description	DiscoGrip™ female disconnect, premium nylon fully insulated, 22 – 18 AWG, .205 x .020 tab size.
Product Type	Disconnects
CSA Certified	Yes
UL Listed	Yes
Height (In.)	.22
Length (In.)	.78
Width (In.)	.31
Max. Ins.	.133
Panduit Color Code	Red
Pricing Description	Female Disconnect, premium nylon fully insulated, 22 18 AWG, .187/.205 x .020 tab size, funnel entry
Tab Size (In.)	.205/.187 x .020
Tool	CT-600-A‡, CT-1525‡, CT-2500‡
Wire Range	22 – 18 AWG
Wire Range (mm ²)	0.5 - 1.0
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.