

Current refinements (click  to remove)

[Search Tips](#)

Region [USA](#)  Product Family [HSTT Heat Shrink 4 ft. Pieces](#)  Text Search: 'HSTT50-48-5C'

Your search criteria matched only one product, shown below.



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT0548-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1(Colors), Class 2 (Clear)

Part Number:	HSTT5048-5C
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink
Material:	Flame retardant polyolefin cross-linked except clear
Color:	Clear
Military Specification:	AMS-DTL-23053/5 Class 2
Length (ft.):	4
Length (m):	1.2
Max. Recovered I.D. (In.):	.250
Max. Recovered I.D. (mm):	6.4
Min. Expanded I.D. (In.):	.500
Min. Expanded I.D. (mm):	12.7
Nominal Diameter / Size:	.500
Nominal Recovered Wall Thickness (In.):	.025
Nominal Recovered Wall Thickness (mm):	.6
Shrink Ratio:	2:1
Temperature Range:	-67°F to 275°F (-55°C to 135°C)
Min. Order UOM:	PC
Min. Order Qty.:	5
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.