

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)  Within Results

 **Text Search: 'HSTT50-48-QC'**

Your search criteria matched only one product, shown below

## HSTT50-48-QC



- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance

For clear, add "C" to end of part number package suffix (Example HSTT05 -48-QC). Contact customer service for additional color information.

Meets Mil Spec AMSDTL-23053/5 Class 1(Colors), Class 2 (Clear)

Part Number	HSTT5048-QC
RoHS Compliancy Status	Compliant
Part Description	Thin Wall Polyolefin Heat Shrink
Material	Flame retardant polyolefin cross-linked except clear
Color	Clear
Military Specification	AMS-DTL-23053/5 Class 2
Length (ft.)	4
Length (m)	1.2
Max. Recovered I.D. (In.)	.250
Max. Recovered I.D. (mm)	6.4
Min. Expanded I.D. (In.)	.500
Min. Expanded I.D. (mm)	12.7
Nominal Diameter / Size	.500
Nominal Recovered Wall Thickness (In.)	.025
Nominal Recovered Wall Thickness (mm)	.6
Pricing Description	Heat Shrink Thin, .50"25Pcs/Pk
Shrink Ratio	2:1
Temperature Range	-67°F to 275°F (-55°C to 135°C)
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.