

Search Results

- Evaluate
- FAQ's
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'HSTTVA100-Y'

Your search criteria matched only one product, shown below

HSTTVA100Y



Dual Wall Polyolefin DAMP-SHRINK™ Heat Shrink Tubing in 6" Pieces

- For damp locations
- Flexible tubing with an adhesive inner wall which seals and protects components from moisture and corrosion
- For use when a flexible adhesive lined tubing is needed
- Material Type: Polyolefin Cross-Linked with adhesive
- Shrink ratio: 2:1
- Temperature range: -67°F to 230°F (-55°C to 110°C)
- Flammability: Outer wall flame retardant
- Voltage rating: 600 V
- Mil Spec: AMSDTL-23053/4 Class 2

▪ Part Number	HSTTVA100-Y
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Dual Wall Adhesive Lined Thin Wall Heat Shrink (UL224 VW)
▪ Material	Polyolefin Cross-linked with adhesive
▪ Color	Black
▪ Military Specification	AMS-DTL-23053/4 Class 2
▪ Length (In.)	6.00
▪ Length (mm)	152.4
▪ Flammability Rating	Outer Wall Flame Retardant
▪ Max. Recovered I.D. (In.)	.500
▪ Max. Recovered I.D. (mm)	12.7
▪ Min. Expanded I.D. (In.)	1.00
▪ Min. Expanded I.D. (mm)	25.4
▪ Nominal Diameter (In.)	1.00
▪ Nominal Diameter (mm)	25.4
▪ Nominal Recovered Wall Thickness (In.)	.046
▪ Nominal Recovered Wall Thickness (mm)	1.2
▪ Pieces per Package	2
▪ Pricing Description	Heat Shrink Thin, Adhesive, 1"(25.4mm) Dia
▪ Shrink Ratio	2:1
▪ Temperature Range	-67°F to 230°F
▪ Min. Order UOM	PK
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.