



Keyword, Part Number or Cross-Ref

All Products Solutions Support



G3X2IB6

Type G Wide Slot Wiring Duct

Panduit® type G wide slot wiring duct, 3 W x 2 H, 6' length, PVC, intrinsic blue.

Specifications

CE Compliant	Yes
CSA Certified	Yes
Color	Intrinsic Blue
Cover Part Number	C3IB6
Flammability Rating	UL94 V-0
Height (In.)	2.12
Height (mm)	53.8
Length (ft.)	6
Length (m)	1.8
Material	Lead-Free PVC

Mounting Method	Standard Mounting Holes
Slot Width (In.)	0.31
Type	Base
UL Recognized (File No. E147128)	Yes
UL recognized continuous use temp	122°F (50°C)
Width (In.)	3.25
Width (mm)	82.6
RoHS Compliancy Status	Compliant
Min. Order Qty.	6

Packaging Details

UPC	61305602297
Std. Pkg. Qty.	6
Std. Pkg. Volume (cf)	0.1766

Std. Ctn. Qty.	120
Std. Ctn. Volume (cf)	3.5311

Resources

Part Drawings	Wide Slot Wiring Duct	US English	PDF 72.11KB		
---------------	-----------------------	------------	-------------	--	--

Related Products

F2X4LG6

The Panduct® type F narrow slot wiring duct has a nominal duct size of 2W x 4H (50.8mm x 101.6mm) and is 6' long. It is light gray and made of PVC.

F3X4LG6

The Panduct® type F narrow slot wiring duct has a nominal duct size of 3W x 4H (76.2mm x 101.6mm) and is 6' long. It is light gray and made of PVC.

F2X3LG6

The Panduct® type F narrow slot wiring duct has a nominal duct size of 2W x 3H (50.8mm x 76.2mm) and is 6' long. It is light gray and made of PVC.



Email Support

Email support available
24/7



800-777-3300

Monday through Friday
7:00 am-6:30 pm CST



Where to Buy

Find a Panduit
Distributor or Partner

ABOUT US

Research and Development
Media Resources
World Headquarters
Awards
Partner Ecosystem

CAREERS AT PANDUIT

THE HUB – PARTNER PORTAL
PRODUCT REGISTRATION
PANDUIT CONNECTIONS BLOG



GET OUR CATALOG

Download the PDF or request a copy be mailed to you.

Which catalog would you like?

▶ DOWNLOAD

▶ REQUEST COPY

