

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFPan-Ty Bow-T ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'PLB4H-TL39'

Your search criteria matched only one product, shown below

PLB4H-TL39



- For high temperature applications up to 239°F (115°C) – indoor use
- A fast and economical method to secure and separate two bundles
- Reduces part number inventory – single part covers multiple bundle sizes
- Installs easily by hand – second loop can be installed with *PANDUIT* cable tie installation tools

Part Number	PLB4H-TL39
RoHS Compliancy Status	Compliant
Part Description	Double Loop Cable Tie, 14.7", Light-Heavy cross section
Product Type	Cable Ties
Material	Heat Stabilized Nylon 6.6
Color	Natural
CSA Certified	Yes
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Length (In.)	14.7
Length (mm)	373
Width (In.)	.300
Width (mm)	7.6
CE Compliant	Yes
Cross Section	Light-Heavy
Head Height (In.)	.322
Head Height (mm)	8.2
Head Length (In.)	1.1
Head Length (mm)	27.9
Head Width (In.)	.490
Head Width (mm)	12.4
Locking Style	Locking
Material Flammability Rating	UL 94V-2
Max. Combined Bundle Dia. (In.)	3.60
Max. Combined Bundle Dia. (mm)	91
Max. Continuous Use Temperature	239°F (115°C)
Min. Loop Tensile Strength (Lbs.)	120
Min. Loop Tensile Strength (N)	534
Pricing Description	Double Loop Tie, 14.7"L (373mm), Light-Heavy, Heat Stabilized, Natural
Thickness (In.)	.075
Thickness (mm)	1.9
Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
Min. Order UOM	PC
Min. Order Qty.	250
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.