

Current refinements (click to remove)

Search Tips

Region **USA** Product Family **Pan-Ty® Wing Push Mount Weather Resistant Cable Ties** Text Search: 'PLWP2H-TL0'

Your search criteria matched only one product, shown below.



- Greater resistance to damage caused by ultraviolet light—indoor or outdoor use
- Cable tie, mount, and fastener in a single part
- Used to attach bundles to another surface such as a flat panel
- Anchor is easily pressed into a pre-formed hole and locks in place
- Wings provide constant tension for a stable, secure and rattle-free installation
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation

Related Products

- [Cable Tie Tools – Tool Contro...](#)
- [Cable Tie Tools – Installer C...](#)
- [Pneumatic Hand Tools - Tool -Control...](#)

Part Number:	PLWP2HTL0
RoHS Compliancy Status:	Compliant
Part Description:	Wing Push Mount Tie, 8.9", Light-Heavy cross section
Product Type:	Cable Ties
Material:	Weather Resistant Nylon 6.6
Color:	Black
CSA Certified:	No
UL Listed (File #E56854):	No
UL Recognized (File #E56854):	No
Length (In.):	8.9
Length (mm):	226
Width (In.):	.300
Width (mm):	7.6
CE Compliant:	Yes
Cross Section:	Light-Heavy
Head Height (In.):	.370
Head Height (mm):	9.4
Locking Style:	Locking
Material Flammability Rating:	UL 94-HB
Max. Bundle Diameter (In.):	2.00
Max. Bundle Diameter (mm):	51
Max. Continuous Use Temperature	185°F (85°C)
Max. Panel Thickness (In.):	.105
Max. Panel Thickness (mm):	2.7
Min. Loop Tensile Strength (Lbs.):	120
Min. Loop Tensile Strength (N):	534
Nominal Hole Diameter (In.):	.266
Nominal Hole Diameter (mm):	6.8
Thickness (In.):	.075
Thickness (mm):	1.9
Tool:	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
Min. Order UOM:	PC
Min. Order Qty.:	250
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to My Catalog	<input type="button" value="e"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.