

Current refinements (click to remove)

[Search Tips](#)

Region **USA** Product Family **Fork Terminals, Nylon Insulated** – Funnel Entry Text Search: 'PNF10-8F-2K'

Your search criteria matched only one product, shown below.



This 3-piece design terminal provides a permanently attached tin plated brass sleeve for insulation grip in funnel or straight entry sleeve designs. This product feature offers the highest quality reliable terminations. Nylon insulation is rated at 600 volts and designed for up to 105° C (221° F) operating temperature.

- Continuously molded design provides reliable, consistent performance through the applicator for a high quality termination every time
- Fork design provides for fast and easy installation, without the need to remove fastener
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V2/HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600 V per UL 486

Part Number:	PNF108F-2K
RoHS Compliancy Status:	Compliant
Part Description:	Fork Terminal, nylon insulated, funnel entry, metal insulation grip sleeve, 12 - 10 AWG wire range, #8 stud size.
Product Type:	Terminals- Reel Fed
CSA Certified:	Yes
UL Listed:	Yes
Length (In.):	1.02
Width (In.):	.37
Barrel to Hole Length (In.):	.78
CA-800 Series Crimp Die:	CD-800-3
CA9 Series Crimp Die:	CD9-3B
Clearance:	.24
Max. Ins.:	.225
Panduit Color Code:	Yellow
Pieces Per Reel:	2000
Stock:	.04
Stud Size:	#8
Wire Range:	12 – 10 AWG
Min. Order UOM:	PC
Min. Order Qty.:	2000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[View Content Details](#)

Evaluate	Design a Solution	Install & Maintain
	Part Drawings: Fork Terminals, Nylon Insulated Funn...	