

**Search Results**

- Evaluate
  - FAQ's
- Design a Solution
  - Part Draw ings
  - PDF-Copper Butt ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'SCS4/0-X'

Your search criteria matched only one product, shown below

**SCS4/0-X**



For Use with Stranded Copper Conductors

- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Internal wire stops to prevent over-insertion of conductor
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV\*\* and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range-taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved

Part Number	SCS4/0-X
RoHS Compliancy Status	Compliant
Part Description	Copper Butt Splice, standard barrel, 4/0 AWG wire.
Product Type	Compression Connectors - Splices
CSA Certified	Yes
UL Listed	Yes
Length (In.)	2.12
Length (mm)	53.8
Copper Conductor Size	4/0 AWG
Barrel O.D.	.71
Barrel I.D.	.56
Panduit Color Code	Purple
Panduit Die Index No.	P54
Pricing Description	Copper Compression Butt Splice, Standard Barrel, 4/0 AWG
Wire Strip Length (In.)	1
Min. Order UOM	PC
Min. Order Qty.	1
Burndy Die Index No.	15
T&B Die Index No.	54
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.