

Search Results

Evaluate

- FAQ's

Design a Solution

- Part Drawings

- PDF Copper Butt ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results

 Text Search: 'SCS8-L'


Your search criteria matched only one product, shown below

## SCS8-L



For Use with Stranded Copper Conductors

- Color-coded barrels marked with *PANDUIT* and specified competitor die index numbers for proper crimp die selection
- Internal wire stops to prevent over-insertion of conductor
- Tin-plated to inhibit corrosion
- UL Listed and CSA Certified to 35 KV\*\* and temperature rated to 90°C when crimped with *PANDUIT* and specified competitor crimping tools and dies
- UL Listed and CSA Certified for wide wire range -taking capability when crimped with *PANDUIT*® *Uni-Die*™ Dieless Crimping Tools‡
- **Tested by Telcordia – meets NEBS Level 3**
- American Bureau of Shipping Approved

|                              |   |
|------------------------------|---|
| Part Number                  | SCS8-L  |
| RoHS Compliancy Status       | Compliant   |
| Part Description             | Copper Butt Splice, standard barrel, #8 AWG wire.                                     |
| Product Type                 | Compression Connectors- Splices   |
| CSA Certified                | Yes   |
| UL Listed                    | Yes   |
| Length (In.)                 | 1.50  |
| Length (mm)                  | 38.1  |
| Copper Conductor Size        | #8 AWG  |
| Barrel O.D.                  | .27   |
| Barrel I.D.                  | .18   |
| Panduit Color Code           | Red   |
| Panduit Die Index No.        | P21   |
| Pricing Description          | Copper Compression Butt Splice, Standard Barrel, #8 AWG                               |
| Wire Strip Length (In.)      | 11/16   |
| Min. Order UOM               | PC  |
| Min. Order Qty.              | 1   |
| Burndy Die Index No.         | 49  |
| T&B Die Index No.            | 21  |
| BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>  |
| Add to Favorite Product List |  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.