

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips  Within Results


 Text Search: 'TMSH50-T300'

Your search criteria matched only one product, shown below

TMSH50-T300



Maintain a standoff from the frame rail in Chassis Tie applications. Ideal for applications where bundles must be secured away from the frame to avoid abrasion.

▪ Part Number	TMSH50T300
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Spacer Mount
▪ Material	Heat Stabilized Nylon 6.6
▪ Color	Black
▪ Height (In.)	1.00
▪ Height (mm)	25.4
▪ Length (In.)	1.00
▪ Length (mm)	25.4
▪ Width (In.)	1.00
▪ Width (mm)	25.4
▪ Environment	Outdoors
▪ Mounting Method	Stud
▪ Panel Hole Diameter (In.)	.50
▪ Panel Hole Diameter (mm)	12.7
▪ Panel Thickness (In.)	.18
▪ Panel Thickness (mm)	4.8
▪ Pricing Description	Tie Mount Spacer Weather Resistant-Heat Stabilized Nylon
▪ Standoff Height (In.)	1.00
▪ Standoff Height (mm)	25.4
▪ Used With Cable Ties	SSPM2.5HL300, SSPM4HL300
▪ Min. Order UOM	PC
▪ Min. Order Qty.	200
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.