

Search within category **GO**

VS-CKBB6-2



VeriSafe Connection Kit for Tapping 6 to 2 AWG conductors.

BUY NOW

DESIGN / INSTALL

Specs	Packaging Details	Documents
Body Hex	5/8	
CE Compliant	No	
CSA Certified	No	
Conductor Size Run	6 AWG / 2 AWG	
Connection Type	Copper to Copper	
Length (In.)	12.75	
Length (mm)	323.85	
Material	Copper (split bolts) / Polypropylene (covers) / Copper Alloy (ferrules)	
Min. Tap with One Max. Run	14 AWG	
Nut Hex	5/8"	
Part Features	Split Bolts (6), Insulating Covers (6), Ferrules (12)	
Product Type	AVT Connection Kit	
Range of Equal Run & Tap Min.	6 AWG	
Range of Equal Run and Tap Max.	2 AWG	
Tightening Torque (In-Lbs)	Split Bolt: 275	
UL Listed	No	
RoHS Compliancy Status	Compliant	
Min. Order Qty.	1	

★ Add to Favorites Add to BOM