


Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFPIGGYBACK DI.
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'DV14-250P-L'

Your search criteria matched only one product, shown below

DV14-250P-L



- Disconnect can be inserted and removed from the male tab without the use of tools for lower installed cost
- Combination of female disconnect and male tab allows versatility in points of connection
- Multiple connection points allow additional circuits to be added to existing equipment without expensive rework
- Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications
- UL Flammability UL 94V -2/HB, maximum insulation temperature 194°F (90°C)
- Rated up to 300 V

Part Number	DV14-250P-L
RoHS Compliancy Status	Compliant
Note	DV14-250P-L replaces DV14-250P-C
Part Description	Piggyback Disconnect, vinyl barrel insulated, 16- 14 AWG, .250 x .032 tab size.
Product Type	Disconnects
CSA Certified	No
UL Listed	No
Length (In.)	0.88
Length (mm)	22.4
Width (In.)	0.29
Width (mm)	7.4
CE Compliant	No
Insulation	vinyl
Max. Ins.	0.160
Max. Ins. (mm)	4.1
Panduit Color Code	Blue
Plating Type	Tinned
Pricing Description	Piggyback Disconnect, vinyl barrel insulated, 16- 14 AWG, .250 x .032 tab size
Tab Size (In.)	0.250 x 0.032
Tab Size (mm)	6.3 x 0.8
Tool	CT-100A, CT-260, CT-1550, CT-1551, CT-2500
Wire Range	16 – 14 AWG
Wire Range (mm²)	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	50
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.