

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFSingle Gang..
 - DWG-Single Gang..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'PRJBX36IW'

Your search criteria matched only one product, shown below

PRJBX36IW




Pan-Way® Power Rated Surface Mount Outlet Boxes are UL 5A listed to 600V and CSA Certified to 300V. For use with LDP, LDS, and T-45. *Pan-Way*® Low Voltage Surface Mount Outlet Boxes are one and two-gang style boxes for low voltage and or fiber optic applications. JBX3510**, JB1**, and JB1D** are supplied with adhesive backing. All surface mount outlet boxes are available in four colors, IW (Off White) with EI (Electric Ivory), IG (International Gray) or WH (White).

- JBP1FS and JBP2FS assemble without the use of screws for faster installation
- JBP1FS and JBP2FS are supplied with adhesive backing to speed installation
- JBP1FS and JBP2FS accept Pan-Way® Snap-on Faceplates for superior aesthetics

All AW (Arctic White) and two and three meter products are only available outside of North America as a standard item. Contact customer service for minimum order quantities, stock and other color availability.

For actual product color please refer to the Surface Raceway Color Chart located in

selection guides.

Part Number	PRJBX36IW
RoHS Compliancy Status	Compliant
Part Description	Single gang two-piece screw together round outlet box. Box accepts UL/CSA devices not to exceed 10 lbs per (5 lbs per CSA). For use with Pan-Way® PD3 or PD6 profile raceway. 5.48"D x 1.14"H (139.2mm x 29.0mm). Breakouts for 3/4" or 1" diameter conduit.
Product Type	Power Rated
Material	PVC
Color	International White
Height (In.)	1.14
Height (mm)	29.0
Length (In.)	5.51
Length (mm)	140.0
Width (In.)	3.28
Width (mm)	83.3
CE Compliant	No
Pricing Description	Single Gang Power Rated Round Junction Box for PD3 / PD6 Raceway
Type	Junction Box
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.