

**Products**

Products Overview

**Product Search**

Evaluate

- FAQ's
- Technical Papers
- PDF Technical Da..

Design a Solution

- Catalog Cut Sheet
- PDF C025X025KBT
- Part Drawings
- PDF C100X050\_\_T..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Products Overview > Product Search >

Current refinements (click  to remove) Search Tips

**C100X050CBT**



- Ideal for temporary marking of chips, boards, IC's
- Label is removable without leaving any residue
- Pliable material is suitable for rough texture surfaces
- Use thermal transfer hybrid ribbon
- UL969 recognized, File # MH14576 & MH14979; cUL recognized, C22.2 No 0.15.01, File # MH14979
- Temperature range: -50°F to 170°F (-10°C to 77°C)
- RoHS Compliant
- Outdoor rated

Part Number	C100X050CBT
RoHS Compliancy Status	Compliant
Note	C100X050CBT replaces TTC88C10 and TTC8G10
Part Description	White, vinyl cloth label
Material	Vinyl Cloth
Height (In.)	0.50
Height (mm)	12.7
Width (In.)	1.00
Width (mm)	25.4
Pricing Description	ThermTrans, Comp Label, Adhesive Vinyl Cloth, 1.00" W x .50" H, White 3" Core
Min. Order UOM	PC
Min. Order Qty.	10000
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.