


Search Results

- Evaluate
- FAQ's
  - Selection Guides
  - PDFConvenience..
- How to Buy
- Bill of Material
  - Favorite Products List
  - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'PV14-P47-E'

Your search criteria matched only one product, shown below

**PV14-P47-E**



- Solid pin designed to prevent damage to the wire from over tightening, resulting in a reliable electrical connection
- Insulation support helps to prevent wire damage in bending applications
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal barrel serrations assure good wire contact and maximum tensile strength
- For use with pin -type terminal blocks
- UL Flammability UL 94V -0, maximum insulation temperature 221°F (105°C)
- UL rated up to 600 V per UL 486A/B, where applicable

Part Number	PV14-P47-E
RoHS Compliancy Status	Compliant
Part Description	Pin Terminal, 16- 14 AWG, vinyl insulated, .49 pin length.
Product Type	Disconnects
Color	Blue
UL Listed	Yes
Length (In.)	0.97
Length (mm)	24.6
Width (In.)	0.07
Width (mm)	1.8
CE Compliant	No
Insulation	Vinyl
Max. Ins.	0.170
Max. Ins. (mm)	4.3
Panduit Color Code	Blue
Pin Length (In.)	0.49
Pin Length (mm)	12.4
Plating Type	Tinned
Pricing Description	Terminal Convenience Package
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
Tool	CT-100A, CT-260, CT-1550, CT-1551, CT-2500
Wire Range	16 – 14 AWG
Wire Range (mm <sup>2</sup> )	1.5 – 2.5
Min. Order UOM	PC
Min. Order Qty.	20
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.