

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

[Home](#) > [Products Overview](#) > [Search Results](#) >

Current refinements (click  to remove) [Search Tips](#)

 **Text Search: 'PVT-44'**


Your search criteria matched only one product, shown below

## PVT-44



All tags have a write-on surface that accepts pen pencil or marker pens. Can be permanently marked with *Panduit*® Marker Pens

- Meet OSHA Standard 1910.147 requirements for tagout applications
- Semi-rigid plastic tags are 3.00" (76.00mm) W x 5.75" (146.00mm) H with a .38" (9.00mm) brass grommet for greater strength and increased durability
- Tags can be attached with a lockout device or with a *PANDUIT* PLT2S nylon tie (50 lb. loop tensile strength) supplied with each tag
- PVT-\* Package consists of five tags and five cable ties
- PVT-\*-Q Package consists of 25 tags and 25 cable ties
- Can be clearly identified with *PANDUIT* permanent marking pens

Part Number	PVT-44
RoHS Compliancy Status	Compliant
Part Description	Plastic Tag, 3.00" x 5.75", «M,27[Quotation mark]Do Not Operate M&M,27[Quotation mark], 5 tags and ties per package.
Material	GMV5 SemiRigid Plastic
Height (In.)	5.75
Height (mm)	146.0
Width (In.)	3.00
Width (mm)	76.0
Color (Legend/Background)	Red and Black/White
Legend	DO NOT OPERATE MAINTENANCE DEPARTMENT
Marker / Tag Style	A
Pricing Description	Plastic Tag, 'Danger Do Not Operate Maintenance ..', 5 tags & ties/pk, RB/WH
Tags & Ties Per Pkg.	5
Min. Order UOM	PK
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.