

Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'TDP43HY'

Your search criteria matched only one product, shown below

TDP43HY



- Rugged, high speed industrial printer
- Thermal transfer printers create crisp, clear legends with superior legibility
- Up to 10.00" per second print speed for fast label production
- Use to print a wide variety of self-laminating labels, component labels, non-laminated labels, marker plate, continuous tapes and heat shrink labels up to 4.00" wide
- *Easy-Mark*TM Labeling Software and hybrid ribbon included with printer

Mechanical Information:

Size: 13.5" H x 10.4" W x 17.0" L

(341mm H x 265mm W x 430mm L)

Weight: 40 lbs. (18kg)

Print Speed: up to 10" (254mm) per second

Media: Roll Width: 1.0" - 5.0" (25mm - 125mm)

Max. Roll Diameter: 8.6" (220mm)

Core Diameter: 1.5" or 3.0" (38mm or 76mm)

Part Number	TDP43HY
RoHS Compliancy Status	Compliant
Note	TDP43HY replaces TDP43H
Part Description	305 dpi printer for high volume applications, <i>PANDUIT</i> [®] Easy-Mark TM Labeling Software, RHH4BLS hybrid black ribbon, AC power adapter and manual.
Pricing Description	Thermal Transfer Desktop Printer, 305 dpi, 120 V, High Volume
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.