

Search Results

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - STPEXtra-Heavy ..
 - PDFEXtra-Heavy ..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips

 Text Search: 'TMEHS8-X0'

Your search criteria matched only one product, shown below

TMEH-S8-X0



Designed for use with Panduit extra -heavy cross section ties for mounting cable, large wire bundles, or tubular shapes.

- Unique cradle design provides maximum stability for cable bundle
- Route and support large diameter and heavy cable bundles

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature TakTy® Hook & Loop Cable Ties.

Part Number	TMEHS8-X0
RoHS Compliancy Status	Compliant
Part Description	Extra Heavy Cable Tie Mount
Product Type	Cable Tie Mounts- Screw Applied
Material	Weather Resistant Nylon 6.6
Color	Black
UL Recognized	E136577
Height (In.)	0.61
Height (mm)	15.5
Length (In.)	1.62
Length (mm)	41.1
Width (In.)	0.72
Width (mm)	18.3
CE Compliant	No
Environment	Outdoor
Flammability Rating	V-2
Hole Diameter (In.)	0.18
Hole Diameter (mm)	4.3
Max. Bundle Diameter (mm)	12.7
Max. Continuous Use Temperature	185°F (85°C)
Mounting Method	#8 (M4) Screw
Pricing Description	Cable Tie Mount, ExtraHeavy, #8 Screw (M4), Weather Resistant Nylon
Screw Size	#8 (M4)
Screw Size Metric	M4
Sub Brand	Cable Tie Mount
Temperature Range	-40°F – 185°F (-40°C – 85°C)
Type	Screw Applied
Used With Cable Ties	I, S, H, EH
Min. Order UOM	PC
Min. Order Qty.	10
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.