Mini-Com® Ultimate ID® Multi-Media/Fiber Surface Mount Box

- Ultimate ID® components are part of a complete system for identification designed to efficiently support TIA/EIA-606-A standard labeling requirements
- Accepts Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Features twelve ports, six on each side, angled to improve bend radius control
- Includes two knockouts which are compatible with Panduit LD5 and LD10 raceway
- Mounts to single or double gang opening

- Mounts easily with supplied mounting screws, adhesive tape, or optional magnet (CSBM-X)
- Supplied with clear station and port label covers, labels sold separately
- Can be clearly identified with the PanTher™ LS8E or Cougar™ LS9 Hand-Held Thermal Transfer Printers
- Non-adhesive computer printable label sheets for desktop printers and write-on labels available
- Replacement label covers available
- Optional icons available

ULTIMATE ID

Part Number	Part Description	Color‡	Labels Required*	Std. Pkg. Qty.	Std. Ctn. Qty.
UICBXA12IW-A	Multi-media surface mount box accepts up to twelve Mini-Com® Modules and includes built-in figure eight spool to help manage fiber cable.	Off White	Two 4-Port Two 6-Port	1	10

‡ For other colors replace suffix IW (Off White) with EI (Electric Ivory) or WH (White).
All surface mount boxes supplied with mounting screws.
*Ultimate ID® Labels can be found on pages O.11 and O.19.

Mini-Com® Multi-Media/Fiber Surface Mount Boxes

- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Mount easily with supplied mounting screws or adhesive tape
- Cable tie slots for improved cable management
- Tamper resistant screw for added security

- Unique built-in fiber spool design secures cable in place and stores up to 78.8 feet (24 meters) of buffered fiber optic cable
- Cable entry from side and rear knockouts and from opening in bottom of base
- Optional adhesive labels available
- Combination label/label cover for custom outlet identification

CBXF6IW-AY

CBXF12IW-AY

Part Number	Part Description	Color‡	Used with Pan-Way® Raceway	Std. Pkg. Qty.	Std. Ctn. Qty.
CBXF6IW-AY	Surface mount box accepts up to six Mini-Com® Modules. Icon slots available for optional icons. 0.99"H x 4.71"W x 6.67"L (25mm x 120mm x 170mm)	Off White	LD3/LD5	1	10
CBXF12IW-AY	Surface mount box accepts up to twelve Mini-Com® Modules. 1.81"H x 4.71"W x 6.67"L (46mm x 120mm x 170mm).	Off White	LD3/LD5/LD10	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).