



**Part Number:** 83030400  
**Description:** IEC 60320 C20 Screw Mount Power Inlet

[Previous](#) [Next](#)



**\*\* Please select your country for pricing and availability \*\***

Select the country you are located in

## Specifications

*(Specifications subject to change without notice)*

<b>Part Number:</b> 83030400
<b>Int'l Current Rating:</b> 16A
<b>Int'l Voltage Rating:</b> 250VAC
<b>N.A. Current Rating:</b> 20A
<b>N.A. Voltage Rating :</b> 250VAC
<b>Temperature Rating:</b> 70°C*
<b>Flammability Rating:</b> UL 94 V-0
<b>Class:</b> I
<b>Quick Disconnects:</b> 3/6.3mm
<b>Solder Tabs:</b> 0
<b>Terminal Material:</b> Nickel-plated brass
<b>Sheet Style:</b> C20
<b>Mounting Style:</b> Screw
<b>General Material:</b> PBT
<b>Color:</b> Black
<b>CE Marking:</b> yes
<b>REMARKS:</b> *Temperature rating is 60°C to 70°C depending on the approval agency. See individual approval documents for temperature ratings.
<b>Last Modification:</b> 02/04/14 • 14:20:16 • dford *Specifications subject to change without notice



Printable version of Specifications

Document Center			
Drawings	Approvals	Environmental	Misc.
AutoCAD (.dwg)	  		Designer Notes
Adobe Acrobat PDF (.pdf)	Click to email approval documents		

Related Items
 56010100 - Green/Yellow PVC Single Wire
 56010110 - Brown PVC Single Wire
 56010120 - Blue PVC Single Wire
 83011380 - IEC 60320 C19 Cable Mount Rewireable Connector

### United States

PO Box 115 | Oskaloosa, IA 52577 | info@interpower.com  
 Toll-Free Phone: (800) 662-2290 | Toll-Free Fax: (800) 645-5360  
 Phone: (641) 673-5000 | Fax: (641) 673-5100

### United Kingdom

10 Kelvin Drive | Knowlhill, Milton Keynes | Buckinghamshire, MK5 8NH | UK | uk@interpower.com  
**UK, Ireland, Germany, Switzerland, Austria**  
 Freephone: 00800 5566 5566 | Freefax: 00800 5655 5655  
**International:** Phone: +44 (0)1908 295 300 | Fax: +44 (0)1908 295301