

Part Number: 83011152

Description: IEC 60320 C13 Rewireable Connector

[Previous](#)

[Next](#)



Please select your country for pricing and availability

Select the country you are located in

Specifications

(Specifications subject to change without notice)

Part Number: 83011152

Int'l Current Rating: 10A

Int'l Voltage Rating: 250VAC

N.A. Current Rating: 10A

N.A. Voltage Rating : 250VAC

Temperature Rating: -40°C to 70°C

Flammability Rating: UL 94 V-0

Class: I

Terminal Material: Brass

Sheet Style: C13

Mounting Style: Cable Mount

General Material: Nylon

Color: Black

CE Marking: yes





REMARKS: Do not use cable sizes that are greater than the I/D of 07.6mm.

Last Modification: 02/11/15 • 13:34:28 • jcaligiu

***Specifications subject to change without notice**



Printable version of Specifications

Document Center			
Drawings	Approvals	Environmental	Misc.
AutoCAD (.dwg)			Wiring Instructions Designer Notes
Adobe Acrobat PDF (.pdf)			
			
	Click to email approval documents		

United States

PO Box 115 | Oskaloosa, IA 52577 | info@interpower.com

Phone: (800) 662-2290 | Fax: (800) 645-5360

United Kingdom

10 Kelvin Drive | Knowlhill, Milton Keynes | Buckinghamshire, MK5 8NH | U.K. | uk@interpower.com

UK, Ireland, Germany, Switzerland, Austria

Freephone: 00800 5566 5566 | Freefax: 00800 5655 5655

International: Phone: +44 (0)1908 295 300 | Fax: +44 (0)1908 295301