



**Part Number:** 83011380  
**Description:** IEC 60320 C19 Cable Mount Rewireable Connector

[Previous](#) [Next](#)



**\*\* Please select your country for pricing and availability \*\***

Select the country you are located in

## Specifications

*(Specifications subject to change without notice)*

<b>Part Number:</b> 83011380
<b>Int'l Current Rating:</b> 16A
<b>Int'l Voltage Rating:</b> 250VAC
<b>N.A. Current Rating:</b> 21A
<b>N.A. Voltage Rating :</b> 125/250VAC
<b>Temperature Rating:</b> 70°C
<b>Flammability Rating:</b> UL 94 V-0
<b>Class:</b> I
<b>Quick Disconnects:</b> 0
<b>Solder Tabs:</b> 0
<b>Terminal Material:</b> Nickel-plated brass
<b>Sheet Style:</b> C19
<b>Mounting Style:</b> Cable Mount
<b>General Material:</b> Polyamide 6
<b>Color:</b> Black
<b>CE Marking:</b> yes
<b>REMARKS:</b>
<b>Last Modification:</b> 11/08/10 • 08:55:49 • jbrown <b>*Specifications subject to change without notice</b>



Printable version of Specifications

Document Center			
Drawings	Approvals	Environmental	Misc.
AutoCAD (.dwg)			Wiring Instructions Designer Notes
Adobe Acrobat PDF (.pdf)	 		
Click to email approval documents			

Related Items
<p>83030440 - IEC 60320 C20 Snap-in Power Inlet</p>
<p>86065030 - International 3x1.5mm² H05VV-F Cable</p>
<p>86065040 - International 3x2.5mm² H05VV-F Cable</p>

### United States

PO Box 115 | Oskaloosa, IA 52577 | info@interpower.com  
 Toll-Free Phone: (800) 662-2290 | Toll-Free Fax: (800) 645-5360  
 Phone: (641) 673-5000 | Fax: (641) 673-5100

### United Kingdom

10 Kelvin Drive | Knowlhill, Milton Keynes | Buckinghamshire, MK5 8NH | UK | uk@interpower.com  
**UK, Ireland, Germany, Switzerland, Austria**  
 Freephone: 00800 5566 5566 | Freefax: 00800 5655 5655  
**International:** Phone: +44 (0)1908 295 300 | Fax: +44 (0)1908 295301